



### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Battery Type	Lead-Acid battery
Provided Equipment	All required connectors Battery recycling guide Installation guide Reusable packaging

### Physical

Height	2.99 in (7.6 cm)
Width	7.99 in (20.3 cm)
Depth	22.99 in (58.4 cm)
Net Weight	49.01 lb(US) (22.23 kg)
Mounting Mode	Not rack-mountable

### Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

### Batteries & Runtime

Battery blocks per string	10
Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Enclosed battery cartridge
Battery Voltage	120 V
RBC Quantity	1

### Ordering and shipping details

GTIN	731304356165
Package weight(Lbs)	55.40 lb(US) (25.13 kg)

### Packing Units

Package 1 Height	8.98 in (22.8 cm)
Package 1 width	15.47 in (39.3 cm)
Package 1 Length	29.96 in (76.1 cm)
Number of Units in Package 3	12

### Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

### Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[APCRBC117US](#)