



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	200 V
Main Output Voltage	200 V
Input Connection Type	IEC 60320 L6-20P
Number of rack unit	0U
Communication port protocol	SNMP Redfish
Provided Equipment	Installation guide Rack Mounting brackets Safety guide

Physical

Color	Black
Height	70.75 in (179.7 cm)
Width	2.17 in (5.5 cm)
Depth	1.81 in (4.6 cm)
Net Weight	12.24 lb(US) (5.55 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Not rack-mountable
USB compatible	No

Input

Line Rated Current	16 A
Acceptable Input Voltage	100...240 V
Input current limits	20 A
Load Capacity	3300 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	21 C13/C15 3 C19/C21
--------------------------------	-------------------------

Conformance

Product Certifications	FCC part 15 class A PSE
------------------------	----------------------------

Environmental

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Batteries & Runtime

Communication Network Type	10/100/1000BASE-T
----------------------------	-------------------

Ordering and shipping details

GTIN	731304412922
Package weight(Lbs)	17.33 lb(US) (7.86 kg)

Packing Units

Package 1 Height	78.82 in (200.2 cm)
Package 1 width	6.50 in (16.5 cm)
Package 1 Length	4.49 in (11.4 cm)
Number of Units in Package 3	48

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[APDU9959J](#)