

## DF2CA10

NFC cartridge fuses, TeSys GS, cylindrical  
10mm x 38mm, fuse type aM, 500VAC, 10A,  
without striker



### Main

|                                |                         |
|--------------------------------|-------------------------|
| Range of Product               | TeSys fuse-disconnector |
| Product or Component Type      | Cartridge fuse          |
| Device short name              | DF2                     |
| [Ue] rated operational voltage | 500 V AC                |
| Fuse size                      | 10 x 38 mm              |
| Fuse type                      | NFC                     |
| Quantity per Set               | Set of 10               |

### Complementary

|                    |                       |
|--------------------|-----------------------|
| Line Rated Current | 10 A 500 V            |
| Fuse curve         | AM                    |
| Net Weight         | 0.02 lb(US) (0.01 kg) |

### Ordering and shipping details

|                   |                             |
|-------------------|-----------------------------|
| Category          | 22621-IEC PANEL ACCESSORIES |
| Discount Schedule | I                           |
| GTIN              | 3389110502022               |
| Returnability     | No                          |
| Country of origin | FR                          |

### Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type of Package 1       | PCE                    |
| Number of Units in Package 1 | 1                      |
| Package 1 Height             | 0.51 in (1.3 cm)       |
| Package 1 Width              | 1.57 in (4.0 cm)       |
| Package 1 Length             | 4.33 in (11.0 cm)      |
| Package 1 Weight             | 0.25 oz (7.0 g)        |
| Unit Type of Package 2       | BB1                    |
| Number of Units in Package 2 | 10                     |
| Package 2 Height             | 0.51 in (1.3 cm)       |
| Package 2 Width              | 1.57 in (4.0 cm)       |
| Package 2 Length             | 4.33 in (11.0 cm)      |
| Package 2 Weight             | 2.72 oz (77.0 g)       |
| Unit Type of Package 3       | S01                    |
| Number of Units in Package 3 | 720                    |
| Package 3 Height             | 5.91 in (15.0 cm)      |
| Package 3 Width              | 5.91 in (15.0 cm)      |
| Package 3 Length             | 15.75 in (40.0 cm)     |
| Package 3 Weight             | 12.76 lb(US) (5.79 kg) |

## Offer Sustainability

|                            |                                                                                                                              |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                        |
| California proposition 65  | WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>                   |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                            |
| REACH free of SVHC         | Yes                                                                                                                          |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>                                                                                |
| Toxic heavy metal free     | Yes                                                                                                                          |
| Mercury free               | Yes                                                                                                                          |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                       |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                          |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| PVC free                   | Yes                                                                                                                          |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[DF2CA10](#)