

G50B-20A2

APC AV 20 Amp G Type Rack Power Filter, 120V



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	120 V
Plug standard	NEMA 5-20P
Number of rack unit	1U
Cable length	8 ft (2.44 m)
Number of cables	1
Provided equipment	User Manual

Physical

Color	Black
Height	1.69 in (4.3 cm)
Width	17.13 in (43.5 cm)
Depth	9.45 in (24 cm)
Net Weight	10.41 lb(US) (4.72 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	50/60 Hz
Switching current capacity	16 A

Output

Number of power socket outlets	9
Outlet standard	NEMA 5-20R (T-Slot)

Conformance

Standards	UL 1449
Equipment protection policy	Lifetime : \$450000
UL 1449 TVSS Rating	330

Environmental

Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...10000 ft (0.00...3048.00 m)
Storage Relative Humidity	0...95 %

Surge Protection and Filtering

Let Through Voltage Rating	40 V
Common mode rejection	55 dB
Surge energy rating	3400 J

Ordering and shipping details

GTIN	731304281191
Package weight(Lbs)	11.73 lb(US) (5.32 kg)

Packing Units

Package 1 Height	3.39 in (8.6 cm)
Package 1 width	21.73 in (55.2 cm)
Package 1 Length	12.99 in (33 cm)
SCC14	10731304281198
Number of Units in Package 2	2
Package 2 Weight	24.73 lb(US) (11.22 kg)
Package 2 Height	7 in (177.80 mm)
Package 2 width	13 in (330.20 mm)
Package 2 Length	22 in (558.80 mm)
Number of Units in Package 3	36

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Under investigation

Contractual warranty

Warranty	Lifetime
----------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[G50B-20A2](#)