



Main

Product or Component Type	Elbow
Range of Product	Powerbus

Complementary

Current Rating	400 A
Busbar Configuration	4A L1 + L2 + N + L3
Busbar Material	Silver plated copper busbar
Integral Ground	50 percent capacity integral ground bus
Voltage Rating	600 V AC
Number of Phases	3 phase
Wiring configuration	4-wire (100 percent neutral)
Enclosure material	Painted aluminium Black
Installation direction	Left

Environment

IP Degree of Protection	IP40
-------------------------	------

Ordering and shipping details

Category	20171-100A & 225A BUSWAY LENGTHS & FITTINGS
Discount Schedule	PE8
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[PBCF4A400ALLB](#)