

SBP3000

APC Service Bypass Panel- 100-240V; 30A;
BBM; Hardwire Input/Output



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	100 V 120 V 230 V
Main Output Voltage	100 V 120 V 230 V
Other Output Voltage	110 V
Output connector type	Hard Wire 3-wire (H N + E) 1
Number of rack unit	2U
Provided Equipment	Installation guide Rack Mounting brackets User Manual

Physical

Color	Black
Height	3.50 in (8.9 cm)
Width	17.01 in (43.2 cm)
Depth	25.00 in (63.5 cm)
Net Weight	26.46 lb(US) (12 kg)
Mounting Support	Wall
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Input Frequency	50/60 Hz
Number of input connectors	1 Hard Wire 3-wire (H N + E)
Max line current	30 A
Input current limits	30 A
Load Power Factor Range	0...1

Output

Maximum Total Current Draw per Phase	30 A
Protection Type	Circuit breaker
Efficiency	99 %

Conformance

Product Certifications	CSA GOST VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Relative Humidity	0...95 %
Operating altitude	0...15000 ft
Ambient Air Temperature for Storage	-40...149 °F (-40...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)





Ordering and shipping details

GTIN	731304212713
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.99 in (20.3 cm)
Package 1 Width	24.02 in (61 cm)
Package 1 Length	39.02 in (99.1 cm)
Package 1 Weight	48.40 lb(US) (21.954 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	12
Package 2 Height	51.97 in (132 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	600.01 lb(US) (272.16 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	2 years (parts only)
----------	----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SBP3000](#)