

SMX2200RMHV2U

APC Smart-UPS X, Line Interactive, 2200VA,
Rack/tower convertible 2U, 208V-230V, 8x
C13+1x C19 IEC, SmartSlot, Extended runtime



Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

Main

Main Input Voltage	208 V 230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	208 V 230 V
Other Output Voltage	220 V 240 V
Rated power in W	1980 W
Rated power in VA	2200 VA
Input Connection Type	IEC 320 C20 Schuko CEE 7 / EU1-16P BS1363A British
Output connection type	8 IEC 320 C13 2 IEC Jumpers 1 IEC 320 C19
Number of rack unit	2U
Cable length	6 ft (1.83 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Smart UPS signalling RS-232 cable User Manual USB cable Rack Mounting brackets

General

Number of power module	1750
Number of power module filled slots	0
Number of power module free slots	0
Product web sub-family	Extended run
Redundant	No

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Physical

Color	Black
Height	3.35 in (8.5 cm)
Width	17.01 in (43.2 cm)
Depth	26.26 in (66.7 cm)
Net Weight	82.28 lb(US) (37.32 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes

Input

Efficiency at full load	140...280 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	2200 VA
Max Configurable Power (Watts)	1980 W
Transfer Time	2-4 ms 6ms typical : 10ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	CE CSA EAC IRAM RCM VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic level	55 dBA
Heat dissipation	150 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery Life	3...5 year(s)
Battery power in VAh	702 VAh runtime

Battery Charge Power (Watts)	233 W rated
Battery option	SMX120RMBP2U 1 2106 VAh SMX120RMBP2U 2 3510 VAh SMX120RMBP2U 3 4914 VAh SMX120RMBP2U 4 6318 VAh SMX120RMBP2U 6 9126 VAh SMX120RMBP2U 8 11934 VAh SMX120RMBP2U 10 14742 VAh

Communications & Management

Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : and Overload Indicators Multi-function LCD status and control console
Emergency Power Off (EPO)	Yes
Free slots	1
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rating	645 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

GTIN	731304272687
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.57 in (24.3 cm)
Package 1 Width	23.46 in (59.6 cm)
Package 1 Length	34.21 in (86.9 cm)
Package 1 Weight	100.00 lb(US) (45.36 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	8
Package 2 Height	43.70 in (111 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	846.58 lb(US) (384 kg)
Pallet unit layers	2
Pallet layers	4

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available
----------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SMX2200RMHV2U](#)