



Main

Range of Product	Modicon M171
Accessory / separate part category	Thermal management accessory
Accessory / Separate Part Type	Probe
Product Specific Application	Temperature control

Complementary

Temperature probe type	NTC
Mounting Support	Cables
Cable length	9.84 ft (3 m) +/- 3 %
Electrical connection	2 conductors cable controller side
Connections - terminals	Cable with wire end ferrule
Fixing Mode	Clip-on
Width	1.57 in (40 mm)
Height	0.16 in (4 mm)

Environment

IP Degree of Protection	IP67
-------------------------	------

Ordering and shipping details

Category	22537-M171 / M172 HVAC CONTROLLERS
Discount Schedule	PC12
GTIN	3606480761737
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.57 in (4.000 cm)
Package 1 Width	4.33 in (11.000 cm)
Package 1 Length	4.92 in (12.500 cm)
Package 1 Weight	1.16 oz (33.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	1.97 in (5.000 cm)
Package 2 Width	4.33 in (11.000 cm)
Package 2 Length	4.92 in (12.500 cm)
Package 2 Weight	6.00 oz (170.000 g)
Unit Type of Package 3	S01
Number of Units in Package 3	60

Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	5.91 in (15.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	4.94 lb(US) (2.241 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[TM1STNTCSF44030](#)