



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Other Output Voltage	240 V
Plug standard	IEC 60320 C14 NEMA 5-15P NEMA L5-30P
Number of cables	1
Provided Equipment	Hardwire panel User Manual Installation guide

Physical

Color	Black
Height	19.61 in (49.8 cm)
Width	15.51 in (39.4 cm)
Depth	3.31 in (8.4 cm)
Net Weight	21.54 lb(US) (9.77 kg)
Mounting Location	Front Side Top
Mounting preference	No preference
Mounting Mode	Not rack-mountable
USB compatible	No

Input

Input Frequency	47...63 Hz
Max line current	20 A

Conformance

Product Certifications	cTUVus
------------------------	--------

Environmental

Ambient Air Temperature for Operation	-13...104 °F (-25...40 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Storage altitude	0...10000 ft (0.00...3048.00 m)

Ordering and shipping details

GTIN	731304264514
Package weight(Lbs)	24.05 lb(US) (10.91 kg)

Packing Units

Package 1 Height	20.98 in (53.3 cm)
Package 1 width	17.52 in (44.5 cm)
Package 1 Length	5.98 in (15.2 cm)
SCC14	10731304264511
Number of Units in Package 3	16

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[UTS6H](#)