

XVC4B5

Harmony XVC, Monolithic precabled tower light, plastic, red orange green blue clear, Ø40, tube mounting, steady, IP23, 24 V AC/DC



Main

Range of Product	Harmony XVC4
Product or Component Type	Complete pre-wired monolithic tower light
Beacon or indicator bank unit type	5 illuminated units
Sound signalling	Without
Mounting diameter	1.57 in (40 mm)
Component name	XVC
Device short name	XVC
Light source	LED steady red LED steady orange LED steady green LED steady blue LED steady clear
Supply circuit type	AC/DC

Complementary

Material	Polycarbonate illuminated unit ABS (acrylonitrile butadiene-styrene) base unit PBT + ABS (UL94HB) top cover SGP (chromium-plated) support tube
Mounting Location	On support tube, 17 mm
Product mounting	On support tube, 17 mm
[Us] rated supply voltage	24 V
[Us] rated supply voltage	24 V
Cable cross section	0.00 in ² (0.33 mm ²)
AWG Gauge	AWG 22
Cable length	23.62 in (600 mm)
Marking	CE
[Uimp] rated impulse withstand voltage	0.8 kV
Current Consumption	125 mA
Flashing frequency	1 Hz
Net Weight	1.28 lb(US) (0.58 kg)
Height	21.40 in (543.5 mm)

Environment

Standards	EN/IEC 61000-6-2 EN/IEC 61000-6-3
Product Certifications	UL
Protective treatment	TC
Ambient Air Temperature for Storage	-31...158 °F (-35...70 °C)
Ambient Air Temperature for Operation	14...122 °F (-10...50 °C)
Electrical shock protection class	Class I EN/IEC 61140
Overvoltage category	Class I EN/IEC 61140
IP degree of protection	IP23 vertical surface installation EN/IEC 60529

Ordering and shipping details

Category	22617-XVC TOWER LIGHTS
Discount Schedule	XV
GTIN	3606480032417
Returnability	No
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.64 in (6.700 cm)
Package 1 Width	29.53 in (75.000 cm)
Package 1 Length	2.68 in (6.800 cm)
Package 1 Weight	21.94 oz (622.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	6.50 in (16.500 cm)
Package 2 Width	30.12 in (76.500 cm)
Package 2 Length	14.17 in (36.000 cm)
Package 2 Weight	15.76 lb(US) (7.149 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	20
Package 3 Height	30.31 in (77.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	50.26 lb(US) (22.798 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information


Contractual warranty

Warranty	18 months
----------	-----------

Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

Dimensions


Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



No. of illuminated units	b Without buzzer (mm)	b Without buzzer (in.)
1 stage	403.50	15.89
2 stages	438.50	17.26
3 stages	473.50	18.64
4 stages	508.50	20.02
5 stages	543.50	21.40

Pre-assembled and Pre-wired Tower Light

Support Tube Mounting



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XVC4B5](#)