



Main

Product range	8501K
Product type	Relay
Relay Type	General purpose
Mounting type	Socket
Contact composition	3PDT
[Uc] control circuit voltage	24 V AC
Pilot light	Indicator light relay energised LED
Manual operator	Without test button

Complementary

Horsepower rating	0.33 Hp 120 V AC 0.5 hp 240 V AC
Breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 10 A 28 V DC resistive control circuit UL 508 10 A 120 V AC resistive control circuit UL 508 6.66 A 240 V AC resistive control circuit UL 508
Maximum switching voltage	300 V AC 30 V DC
Contact material	Silver tin oxide
Operating time	12 ms - pick-up 12 ms - drop-out
Shape of pins	Tubular
For use with	8501NR61 8501NR62

Environment

Ambient temperature range - operational	-40...113 °F (-40...45 °C)
Product certifications	UL Listed UL Recognized CE CSA
Height	2.66 in (67.56 mm)
Width	1.39 in (35.31 mm)
Depth	1.39 in (35.31 mm)

Ordering and shipping details

Category	21141-8501 KP
Discount Schedule	CP2
GTIN	785901490647
Number of Units in Package 1	1
Package 1 Weight	3.20 oz (90.718 g)
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.60 in (4.064 cm)
Package 1 Width	1.60 in (4.064 cm)
Package 1 Length	2.90 in (7.366 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[8501KP13P14V14](#)