



### Main

Device short name	C
Series name	Heavy duty

### Complementary

Line Rated Current	10 A
Body Material	Zinc alloy
Contact code designation	R300 A600
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Maximum displacement angle	90 °
Specificity of operator	Standard pre-travel
Switch actuation	CCW
Tilting angle	10 °
Torque Value	4 lbf.in (0.45 N.m)
Tripping angle	4 °

### Environment

Ambient air temperature for operation	-20...185 °F (-29...85 °C)
Environmental characteristic	Hazardous location
Product Certifications	CE CSA UL Listed

### Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901146728
Nbr. of units in pkg.	1
Package weight(Lbs)	2.5 lb(US) (1.13 kg)
Returnability	No
Country of origin	MX

### Packing Units

Package 1 Height	6.99 in (17.742 cm)
Package 1 width	2.75 in (6.985 cm)
Package 1 Length	17.74 in (45.064 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9007CR61B1](#)