

Product data sheet

Characteristics

7B2

9007MS/ML limit switch lever - zinc - fixed length - outside steel roller

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	9007
Series name	Miniature potted
Product or component type	Limit switch lever
Device short name	9007MS/ML
Associated complete product	9007MS04.. 9007ML04..
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 0.88 in -
Type of roller	1 steel outside roller diameter: 0.75 in - width: 0.5 in
Type of approach	Lateral approach
Positive opening	Without

Complementary

Tracks	1.375 in
Switch actuation	By 30° cam
Product weight	0.1 lb(US)

Environment

Ambient air temperature for operation	-40...221 °F
Ambient air temperature for storage	-40...221 °F
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22421 - LIMIT SWITCHES,ARMS FOR 9007MS
Discount Schedule	DS1
GTIN	00785901121657
Nbr. of units in pkg.	1
Package weight(Lbs)	0.10000000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[7B2](#)