

9007AO2

snap switch, 9007AO, plunger head, 1 NO and 1 NC contact, 15 A at 120 VAC, 600 VAC maximum



Product availability: Stock - Normally stocked in distribution facility



Main

Range of product	9007
Series name	Heavy duty
Product or component type	Snap basic limit switch
Device short name	9007AO/CO
Body type	Fixed

Complementary

Mounting mode	-
Operator profile	Plunger head
Material	Metal
Body material	Cast zinc
Operator material	Cast zinc
Fixing mode	By the body
Movement of operating head	Linear
Type of operator	Plastic spring return plunger with thermoplastic end
Switch actuation	On end
Type of approach	1 direction vertical approach
Electrical connection	1...2 cables 6 binder head screw terminals (AWG 22...AWG 14)
Number of poles	1
Contacts type and composition	NC-NO, switch function: SPDT-DB
Contact form	Form Z
Contact operation	Snap action
Number of steps	1
Contacts material	Silver contacts
Positive opening	Without
Terminals description ISO n°1	(1-2)NC (3-4)NO
Minimum force for tripping	0.63 lbf
Maximum force for tripping	0.88 lbf
[Ie] rated operational current	6 A at 480 V AC, A600 conforming to NEMA rating designation 10 A at 240 V AC, A600 conforming to NEMA rating designation 15 A at 120 V AC, A600 conforming to NEMA rating designation 0.1 A at 250 V DC 0.25 A at 125 V DC 5 A at 600 V AC, A600 conforming to NEMA rating designation
[Ithe] conventional enclosed thermal current	15 A
[Ui] rated insulation voltage	600 V - for contact block (degree of pollution: 3) conforming to UL 508 600 V - for contact block conforming to CSA C22.2 No 14
Width	0.83 in
Height	2.5 in

Depth	1.03 in
Product weight	0.1 lb(US)


Environment

NEMA degree of protection	NEMA 1 conforming to Nema type 250
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...185 °F
Ambient air temperature for storage	-20...185 °F

Ordering and shipping details

Category	21491 - 9007 A SNAP SWITCHES
Discount Schedule	DS1
GTIN	00785901759126
Nbr. of units in pkg.	1
Package weight(Lbs)	0.10000000000000001
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1150 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9007AO2](#)