

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	9007
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	9007T/FT
Associated head	9007AS9 9007BS9 9007CS9 9007NS9 9007T10S9 9007T5S9
Associated complete product	9007T 9007FT 9007C..S9
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 2.5 in - off-set: - convertible rollers, 2 on same side
Type of roller	2 steel outside roller (convertible) diameter: 0.75 in - width: 0.25 in
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Product weight	0.1 lb(US)

Environment

Ambient air temperature for operation	-10...185 °F
Ambient air temperature for storage	-10...185 °F
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21494 - 9007 ARMS FOR FT,T
Discount Schedule	DS1
GTIN	00785901888017
Nbr. of units in pkg.	1
Package weight(Lbs)	0.23000000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and

----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9007B22](#)