

Product data sheet

Characteristics

9050JCK31V20

Plug-In Timer - Interval - 0.1-10 seconds -
120VAC/110VDC



Product availability: Stock - Normally stocked in distribution facility



Main

Product range	9050JCK
Product type	Timer
Timing mode	Interval
Timing range	0.1...10 s
Supply voltage	110 V DC 120 V AC

Complementary

Power consumption	2 VA
Line Rated Current	10 A
Switch function	DPDT
Contact composition	2 NO + 2 NC
Contact material	Silver nickel
Maximum switching voltage	240 V AC
Mounting type	Socket
Number of pins	8
Shape of pins	Tubular
For use with	8501NR51 8501NR52

Environment

Certifications	CE RoHS UL listed UL recognized
Ambient temperature range - operational	-18...150 °F
Height	2.4 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

Ordering and shipping details

Category	21651 - 9050 JCK(NOT JCK60, 70) G P TIMERS
Discount Schedule	CP2
GTIN	00785901032809
Nbr. of units in pkg.	1
Package weight(Lbs)	0.26000000000000001
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9050JCK31V20](#)