

Product availability: Stock - Normally stocked in distribution facility



### Main

Range	Linergy
Product name	HK
Product or component type	Mounting plate
Poles description	3P
[I <sub>th</sub> ] conventional free air thermal current	25 A
I <sup>2</sup> t on activation	200000 A <sup>2</sup> .s
Number of cables	3 cable(s) 0.01 in <sup>2</sup> (4 mm <sup>2</sup> ) at 221 °F (105 °C)
Width	2.13 in (54 mm)
Height	4.13 in (105 mm)
Depth	2.4 in (61 mm)

### Complementary

[Ui] rated insulation voltage	690 V conforming to IEC 60439-1
9 mm pitches	6

### Environment

Standards	IEC 60439
Product certifications	LROS (Lloyds register of shipping) DNV CSA UL

### Ordering and shipping details

Category	22623 - PANEL BUS (AK5)
Discount Schedule	I11
GTIN	00785901576709
Nbr. of units in pkg.	1
Package weight(Lbs)	0.4899999999999999
Returnability	Y
Country of origin	FR

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AK5PA231](#)