

**Schneider Electric USA**

1415 South Roselle Road

Palatine, IL 60067

Customer Care Center: 1-888-778-2733

Web: www.schneider-electric.us

---

**Item # ATV312H055N4, Variable Speed Drive**

---



**Variable Speed Drive**

Variable Speed Drive

---

**SPECIFICATIONS**

---

Family	Altivar 312
Product Line	AC Drives
Output Ampere Rating	1.9
Application	Constant Torque
Enclosure Rating	IP20
Frame Size	6
HP Rating	0.75
kW Rating	0.55
Voltage Rating	400/480VAC
Input Phase	3 Phase
Output Phase	3 Phase
Control Voltage	24Vdc
Logic Input	6
Analog Input	3

Analog Output	1
Logic/Relay Outputs	1 Form C, 1 NO
Weight [lb]	2.98
Weight [kg]	1.35
UL File No.	E116875
CSA File	1464725
Other	CE, GOST, RoHS, NOM, EMITECH
Communication	Modbus and CANopen

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ATV312H055N4](#)