

VW3A31401

additionnal EMC filter S3 S4 M2 - 1-phase
supply - 9 A



Main

Range of Product	Altivar
Product or Component Type	EMC input filter
Range Compatibility	Lexium SD3 Altivar 312 Solar Lexium 23 Plus Altivar Machine ATV320 Altivar 312 Altivar 31C Lexium 05
Product compatibility	Servo drive LXM230.1 kW Servo drive LXM230.2 kW Servo drive LXM230.4 kW ATV312H018M2 ATV312H037M2 ATV312H055M2 ATV312H075M2 ATV31C018M2 ATV31C037M2 ATV31C055M2 ATV31C075M2 LXM05AD10F1 LXM05AD10M2 LXM05BD10F1 LXM05BD10M2 LXM05CD10M2 Variable speed drive ATV320...C0.18 kW, 200...240 V single phase Variable speed drive ATV320...C0.37 kW, 200...240 V single phase Variable speed drive ATV320...C0.55 kW, 200...240 V single phase Variable speed drive ATV320...C0.75 kW, 200...240 V single phase Variable speed drive ATV320...W/ ATV320...WS0.18 kW, 200...240 V single phase Variable speed drive ATV320...W/ ATV320...WS0.37 kW, 200...240 V single phase Variable speed drive ATV320...W/ ATV320...WS0.55 kW, 200...240 V single phase Variable speed drive ATV320...W/ ATV320...WS0.75 kW, 200...240 V single phase
Product Specific Application	Radio interference input filter
Line Rated Current	9 A
Thermal losses	3.7 W ATV31C018M2
Phase	Single phase

Complementary

Maximum earth leakage current	100 mA 50 Hz
Power supply voltage	200...240 V
Tolerance	10 %
Net Weight	1.32 lb(US) (0.6 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IP degree of protection	IP20 IP41 upper part)
Relative humidity	0...93 % IEC 68-2-3
Ambient air temperature for operation	14...122 °F (-10...50 °C)
Ambient Air Temperature for Storage	-13...158 °F (-25...70 °C)
Operating altitude	<= 3280.84 ft (1000 m) without current derating 3280.84...9842.52 ft (1000...3000 m) with current derating 1 % per 100 m
Vibration resistance	1 gn 13...150 Hz)IEC 60068-2-6 1.5 mm peak to peak 3...13 Hz)IEC 60068-2-6
Shock resistance	15 gn 11 ms EN/IEC 60068-2-27
Standards	EN 133200 EN/IEC 61800-3

Ordering and shipping details

Category	22154 - ATV320/ATV312/ATV32 ACCESSORIES
Discount Schedule	CP4B
GTIN	3389110688948
Nbr. of units in pkg.	1
Package weight(Lbs)	17.60 oz (499 g)
Returnability	No
Country of origin	TH

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.97 in (5 cm)
Package 1 width	7.36 in (18.7 cm)
Package 1 Length	9.45 in (24 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	7
Package 2 Weight	8.88 lb(US) (4.027 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Unit Type of Package 3	P06
Number of Units in Package 3	56
Package 3 Weight	92.92 lb(US) (42.148 kg)
Package 3 Height	30.31 in (77 cm)
Package 3 width	23.62 in (60 cm)
Package 3 Length	31.50 in (80 cm)

Offer Sustainability


California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Additional EMC Input Filters

Dimensions



Dimensions in mm


a	b	c	G	H	Ø
72	195	37	52	180	4.5

Dimensions in in.


a	b	c	G	H	Ø
2.83	7.68	1.46	2.05	7.09	0.18

Additional EMC Input Filter

Mounting the Filter under the Drive



Mounting the Filter next to the Drive



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[VW3A31401](#)