


Product availability: Stock - Normally stocked in distribution facility



Main

Range of product	Altivar
Product or component type	Encoder interface card
Range compatibility	Altivar 61Q Altivar 71Q Altivar Lift Altivar 71 Altivar 61
Discrete output type	Push-pull
[Us] rated supply voltage	24 V DC (voltage limits: 20...30 V)
Number of pulses per revolution	<= 10000 ATV71H.....383 <= 5000 all ATV61 drives <= 5000 ATV71H...M3 <= 5000 ATV71H...M3X <= 5000 ATV71H...N4

Complementary

Supply current	<= 0.175 A
Protection type	Short-circuit protection Overload protection
Maximum operating frequency	300 kHz
Input signal	A B Compliment of A Compliment of B/AB/A
Input impedance	1000 Ohm
Voltage state 0 guaranteed	<= 1.5 V
Voltage state 1 guaranteed	> 11.5...< 25 V
Electrical connection	Terminal, connection capacity: 0.2 mm ² (AWG 24) 500 m cable length (encoder 100 mA) at 14 V

Ordering and shipping details

Category	22135 - ATV61-71 ACCESSORIES
Discount Schedule	CP4C
GTIN	00785901526919
Nbr. of units in pkg.	1
Package weight(Lbs)	0.3599999999999999
Returnability	Y
Country of origin	ID

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[VW3A3407](#)