

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Device short name	C
Head type	Type C turret head rotary lever
Provided equipment	Receptacle
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Cable entry	0.5 in NPT conduit entry
Contact code designation	A600 R300
Contact form	Form ZZ DPDT-DB switch function
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Contacts type and composition	2 NO/2 NC
Maximum displacement angle	90 °
Pilot light	Without pilot lamp
Switch actuation	CW and CCW
Tilting angle	45 °
Torque value	3 lbf.in

Environment

Ambient air temperature for operation	-20...185 °F
Environmental characteristic	Hazardous location
Product certifications	CE CSA UL listed

Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901711551
Nbr. of units in pkg.	1
Package weight(Lbs)	2.5
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9007CR61CS18](#)