

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Device short name	C
Head type	Turret head rotary lever type T/FT
Series name	Heavy duty

### Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Contact code designation	A600 R300
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Maximum displacement angle	90 °
Specificity of operator	Standard pre-travel First stage : 10° - second stage : 2.5°
Switch actuation	CW and CCW
Torque value	4 lbf.in
Tripping angle	4 °
Type of operator	Drive shaft with T-FT hub

### Environment

Ambient air temperature for operation	-20...185 °F
Environmental characteristic	Hazardous location
Product certifications	CE CSA UL listed

### Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901348368
Nbr. of units in pkg.	1
Package weight(Lbs)	2.5
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9007CR65B2S9](#)