

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Bezel material	Chromium plated metal
Device short name	K
Enclosure type	Weatherproof enclosure dust and oil resistant in-door/outdoor
Mounting diameter	1.18 in (30 mm)

Complementary

Contacts type and composition	Without contact block
Light block supply	Direct 120 V
Operator position information	3 positions
Operator profile	Standard knob
Operator profile	1 projecting push-button
Type of operator	Maintained

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901531678
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5500000000000004
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001K43J38LGG](#)