

Product data sheet

Characteristics

TCSECU3M3M5S4

Ethernet ConneXium cable - shielded twisted pair - 2 x rugged RJ45 - UL - 5 m

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	ConneXium
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Product or component type	Shielded twisted pair straight cable
Accessory / separate part destination	Ethernet network
Cable length	16.4 ft (5 m)

Complementary

Transmission support medium	Twisted shielded pairs cable
Communication network category	5e
AWG gauge	AWG 24
Electrical connection	2 connectors RJ45 8 straight
Marking	UL
Cover material	PVC

Environment

IP degree of protection	IP20
Standards	CMG FT4 UL 444 EIA/TIA-568 category CAT 5E IEC 11801 class D EN 50173 class D

Ordering and shipping details

Category	18225 - PLC NTRWK HRDWR & PROWORX SOFTWARE
Discount Schedule	PC41
GTIN	00785901321453
Nbr. of units in pkg.	1
Package weight(Lbs)	0.57000000000000006
Returnability	N
Country of origin	TH

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[TCSECU3M3M5S4](#)