



Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	DA1
Product or component type	Thermistor probe
Device short name	DA1TT
Accessory / separate part category	Protection accessory
Quantity per set	Set of 10
Ambient air temperature for operation	284 °F (140 °C)

Complementary

[Ui] rated insulation voltage	2500 V
[Ue] rated operational voltage	<= 2.5 V
Resistance	250 Ohm per probe 25 °C
Insulation	Reinforced
Cable length	3.28 ft (1 m) between probe and motor terminal plate 9.84 in (250 mm) between probes
Product weight	0.02 lb(US) (0.01 kg)

Environment

Standards	IEC 60034-11 Mark A
-----------	---------------------

Ordering and shipping details

Category	22339 - THERMISTOR RELAY (LT3)
Discount Schedule	I11
GTIN	00785901531876
Nbr. of units in pkg.	10
Package weight(Lbs)	0.01
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0841 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[DA1TT140](#)