



Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

|                                       |                      |
|---------------------------------------|----------------------|
| Range of product                      | DA1                  |
| Product or component type             | Thermistor probe     |
| Device short name                     | DA1TT                |
| Accessory / separate part category    | Protection accessory |
| Quantity per set                      | Set of 10            |
| Ambient air temperature for operation | 338 °F (170 °C)      |

### Complementary

|                                |                                                                                         |
|--------------------------------|-----------------------------------------------------------------------------------------|
| [Ui] rated insulation voltage  | 2500 V                                                                                  |
| [Ue] rated operational voltage | <= 2.5 V                                                                                |
| Resistance                     | 250 Ohm per probe 25 °C                                                                 |
| Insulation                     | Reinforced                                                                              |
| Cable length                   | 3.28 ft (1 m) between probe and motor terminal plate<br>9.84 in (250 mm) between probes |
| Product weight                 | 0.02 lb(US) (0.01 kg)                                                                   |

### Environment

|           |                     |
|-----------|---------------------|
| Standards | IEC 60034-11 Mark A |
|-----------|---------------------|

### Ordering and shipping details

|                       |                                |
|-----------------------|--------------------------------|
| Category              | 22339 - THERMISTOR RELAY (LT3) |
| Discount Schedule     | I11                            |
| GTIN                  | 00785901531906                 |
| Nbr. of units in pkg. | 10                             |
| Package weight(Lbs)   | 0.01                           |
| Returnability         | N                              |
| Country of origin     | FR                             |

### Offer Sustainability

|                                  |                                                                                                                                    |
|----------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status         | Green Premium product                                                                                                              |
| RoHS (date code: YYWW)           | Compliant - since 0841 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold                                                                                  |
| Product environmental profile    | Available                                                                                                                          |
| Product end of life instructions | Available                                                                                                                          |
| California proposition 65        | WARNING: Cancer - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>                                               |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[DA1TT170](#)