



Main

Range of product	EcoStruxure operator terminal Expert
Product or component type	License
Language	Spanish Portuguese Italian French English Chinese German
Format	Paper
Previous software version	V3.0

Complementary

Software designation	EcoStruxure Operator Terminal Expert
Type of license	Single (1 seat)
Software version	V3.1
System requirements	> 1 GB HDD storage device Windows 7 Professional 32/64 bit, > 4 GB primary memory > 1 GB HDD storage device Windows 8.1, > 4 GB primary memory
Communication port protocol	SoMachine network CS/CJ series Ethernet IQ-R/F series Ethernet FX series computer link PacDrive CS/CJ series HOST link Uni-Telway ROC Plus SIO CS/CJ/NJ series Ethernet/IP Q series QnU CPU Ethernet Simatic S7 Ethernet Q/QnA Series Ethernet FX series CPU direct Q series CPU direct DH485 FX series Ethernet Q/QnA series serial Modbus SIO ASCII master Modbus SIO slave Modbus TCP master Modbus SIO master ROC Plus Ethernet Modbus TCP slave Simatic S7 MPI direct EtherNet/IP Zelio Logic A series Ethernet TIA portal Ethernet EtherNet/IP EtherNet/IP EtherNet/IP
Provided equipment	User's documentation in electronic format EcoStruxure operator terminal Expert
Software function	32768 alarms 26 type of fonts 32768 variables

Environment

Image import standard	PNG
-----------------------	-----

Ordering and shipping details

Category	22569 - MAGELIS XBT-GT (AND XBT-G)
Discount Schedule	MC2
GTIN	00785901625377
Nbr. of units in pkg.	1
Package weight(Lbs)	0.12 lb(US) (0.05 kg)
Returnability	Yes
Country of origin	FR

Packing Units

Package 1 Height	0.16 in (4.000 mm)
Package 1 width	6.89 in (175.000 mm)
Package 1 Length	9.84 in (250.000 mm)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric:

HMIEELCZLSPMZZ