

Product availability: Stock - Normally stocked in distribution facility



Main

Range	TeSys
Device short name	GVAE
Product or component type	Auxiliary contact block
Product compatibility	LS1D32 GV3P GV2P GV2RT GV2L GV2ME GV3L GV2LE
Mounting location	Front side
Pole contact composition	2 NO
Connections - terminals	Screw clamp terminals 1 cable 0...0 in ² (0.75...2.5 mm ²) - cable stiffness: flexible - without cable end Screw clamp terminals 2 cable 0...0 in ² (0.75...2.5 mm ²) - cable stiffness: flexible - without cable end Screw clamp terminals 1 cable 0...0 in ² (0.75...1.5 mm ²) - cable stiffness: flexible - with cable end Screw clamp terminals 1 cable 0...0 in ² (1...2.5 mm ²) - cable stiffness: solid Screw clamp terminals 2 cable 0...0 in ² (1...2.5 mm ²) - cable stiffness: solid
Quantity per set	Set of 10

Complementary

[Ui] rated insulation voltage	300 V - conforming to UL 508 300 V - conforming to CSA C22.2 No 14 250 V - conforming to IEC 60947-1
System Voltage	24...240 V AC 24...60 V DC
[Ith] conventional free air thermal current	2.5 A
Protection type	GG fuse 10 A GB2CB06 circuit breaker 10 A
Mechanical durability	100000 cycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Rated operational power in VA	120 VA at 110...120 V AC-15 - electrical durability: 100000 cycles 120 VA at 230...240 V AC-15 - electrical durability: 100000 cycles 48 VA at 24 V AC-15 - electrical durability: 100000 cycles 60 VA at 48 V AC-15 - electrical durability: 100000 cycles
Rated operational power in W	15 W at 48 V DC-13 - electrical durability: 100000 cycles 24 W at 24 V DC-13 - electrical durability: 100000 cycles 9 W at 60 V DC-13 - electrical durability: 100000 cycles
Tightening torque	1.4 N.m - on screw clamp terminals
Height	0.43 in (11 mm)
Width	1.77 in (45 mm)
Depth	1.14 in (29 mm)
Product weight	0.04 lb(US) (0.02 kg)

Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901343462
Nbr. of units in pkg.	1
Package weight(Lbs)	5.0000000000000003E-2
Returnability	Y
Country of origin	CZ


Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

GVAE20



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GVAE20](#)