

9013GHG3J57X

PRESSURE SWITCH 575VAC 5HP G +OPTIONS

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Device short name	G
Enclosure type	Enclosure standard environment indoor
Factory modification	2-way pressure release valve
Product specific application	Control electrically driven water pumps and air compressors
Range of product	Square D Pumptrol
Switch application	Standard

Complementary

Adjustable range on rising pressure	65...200 psi
Approximate adjustable differential	20...40 psi
Depth	3.68 in
Electrical connection	Screw clamp terminal
Fixing mode	By brackets
Fluid connection type	0.375 inch NPSF internal
Height	5.72 in
Material	Zinc plated steel flange
Materials in contact with fluid	Nitrile (Buna-N) diaphragm
Maximum pressure	300 psig
Motor power hp	3 hp 115 V AC 3 phases 5 hp 460/575 V AC 3 phases 5 hp 460/575 V AC 1 phase 2 hp 115 V AC 1 phase 3 hp 230 V AC 1 phase 5 hp 230 V AC 3 phases
Number of poles	2
Permissible voltage	<= 575 V AC
Pressure actuator	Diaphragm
Pressure setting range	120...150 psi
Product weight	2.25 lb(US)
Range on decreasing pressure	40...170 psi
Switch function	DPST
Width	3.44 in

Environment

NEMA degree of protection	NEMA 1
Product certifications	UL listed file E12158 CCN NKPZ CSA file LR25490

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	21536 - 9013 G COMMERCIAL PRESSURE SWITCH
Discount Schedule	CP7G
GTIN	00785901559856
Nbr. of units in pkg.	1
Package weight(Lbs)	2
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference contains SVHC above the threshold - Go to CaP for more details- Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - Substance 2	Di-isodecyl phthalate (DIDP) which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric:

9013GHG3J57X