

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

|                           |                             |
|---------------------------|-----------------------------|
| Range of product          | Harmony 9001K               |
| Product or component type | Illuminated selector switch |
| Device short name         | 9001K                       |
| Type of operator          | Stay put                    |
| Operator profile          | Long handle green           |

### Complementary

|                               |                                  |
|-------------------------------|----------------------------------|
| Bezel material                | Chromium plated metal            |
| Mounting diameter             | 1.18 in (30 mm)                  |
| Product weight                | 0.54 lb(US) (0.245 kg)           |
| Shape of signaling unit head  | Octagonal                        |
| Operator position information | 2 positions                      |
| Contacts type and composition | Without contact block            |
| Mechanical durability         | 500000 cycles                    |
| Light block supply            | Direct                           |
| Light source                  | LED                              |
| Bulb base                     | BA 9s                            |
| Light block colour            | Green                            |
| [Us] rated supply voltage     | 24 V AC/DC                       |
| Product compatibility         | 9001KA2, mounting on side 1 or 2 |
| Device presentation           | Basic element                    |

### Environment

|                                       |                                                                                                                |
|---------------------------------------|----------------------------------------------------------------------------------------------------------------|
| Protective treatment                  | TC                                                                                                             |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)                                                                                     |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C)                                                                                     |
| Electrical shock protection class     | Class II conforming to IEC 61140                                                                               |
| IP degree of protection               | IP66 conforming to IEC 60529                                                                                   |
| NEMA degree of protection             | NEMA 1<br>NEMA 12<br>NEMA 13<br>NEMA 2<br>NEMA 3<br>NEMA 3R<br>NEMA 4                                          |
| Standards                             | EN/IEC 60947-5-1<br>EN/IEC 60947-5-4<br>JIS C 4520<br>CSA C22.2 No 14<br>EN/IEC 60947-1<br>JIS C 852<br>UL 508 |
| Product certifications                | UL 508<br>NEMA                                                                                                 |
| Vibration resistance                  | 7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6                                                              |
| Shock resistance                      | 50 gn conforming to IEC 60068-2-27                                                                             |

## Ordering and shipping details

|                       |                               |
|-----------------------|-------------------------------|
| Category              | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule     | CS1                           |
| GTIN                  | 00785901934097                |
| Nbr. of units in pkg. | 1                             |
| Package weight(Lbs)   | 0.37                          |
| Returnability         | N                             |
| Country of origin     | MX                            |

## Offer Sustainability

|                            |                                                                                                                                    |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| RoHS (date code: YYWW)     | Compliant - since 0921 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a> |
| REACH                      | Reference not containing SVHC above the threshold                                                                                  |
| California proposition 65  | WARNING: This product can expose you to chemicals including:                                                                       |
| - - - - - Substance 1      | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.   |
| - - - - - Substance 2      | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.         |
| - - - - - More information | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                      |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001K11J35LGFG](#)