

# 9001K3L1C

## PUSHBUTTON OPERATOR 30MM TYPE K +OPTIONS

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

|                                 |                                  |
|---------------------------------|----------------------------------|
| Range of product                | Harmony 9001K                    |
| Product or component type       | Complete illuminated push-button |
| Device short name               | 9001K                            |
| Bezel material                  | Chromium plated metal            |
| Mounting diameter               | 1.18 in (30 mm)                  |
| Operator additional information | Extended metallic guard          |
| Light source                    | Incandescent                     |

### Complementary

|                              |                                                                   |
|------------------------------|-------------------------------------------------------------------|
| Shape of signaling unit head | Round                                                             |
| Type of operator             | Spring return                                                     |
| Operator profile             | Flush clear unmarked                                              |
| Bulb base                    | BA 9s                                                             |
| Light block supply           | Via integral transformer (f = 50/60 Hz), (secondary voltage= 6 V) |
| Mechanical durability        | 5000000 cycles                                                    |
| Operating position           | Any position                                                      |
| Product weight               | 0.37 lb(US) (0.166 kg)                                            |

### Environment

|                                       |                                                                                                                |
|---------------------------------------|----------------------------------------------------------------------------------------------------------------|
| Standards                             | EN/IEC 60947-1<br>EN/IEC 60947-5-1<br>EN/IEC 60947-5-4<br>JIS C 4520<br>JIS C 852<br>UL 508<br>CSA C22.2 No 14 |
| Product certifications                | NEMA<br>UL 508                                                                                                 |
| Protective treatment                  | TC                                                                                                             |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)                                                                                     |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C)                                                                                     |
| Vibration resistance                  | 7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6                                                              |
| Shock resistance                      | 50 gn conforming to IEC 60068-2-27                                                                             |
| Electrical shock protection class     | Class II conforming to IEC 61140                                                                               |
| IP degree of protection               | IP66 conforming to IEC 60529                                                                                   |
| NEMA degree of protection             | NEMA 1<br>NEMA 12<br>NEMA 13<br>NEMA 2<br>NEMA 3<br>NEMA 3R<br>NEMA 4                                          |

## Ordering and shipping details

|                       |                               |
|-----------------------|-------------------------------|
| Category              | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule     | CS1                           |
| GTIN                  | 00785901932260                |
| Nbr. of units in pkg. | 1                             |
| Package weight(Lbs)   | 0.5                           |
| Returnability         | N                             |
| Country of origin     | MX                            |

## Offer Sustainability

|                            |                                                                                                                                  |
|----------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65  | WARNING: This product can expose you to chemicals including:                                                                     |
| - - - - - Substance 1      | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| - - - - - More information | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                    |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001K3L1C](#)