



## Main

|                           |                                  |
|---------------------------|----------------------------------|
| Range of Product          | Harmony 9001K                    |
| Product or Component Type | Mushroom head push-button        |
| Device short name         | 9001K                            |
| Type of operator          | push-pull                        |
| Operator profile          | White mushroom Ø 41 mm, unmarked |

## Complementary

|                               |                        |
|-------------------------------|------------------------|
| Bezel material                | Chromium plated metal  |
| Mounting diameter             | 1.18 in (30 mm)        |
| Net Weight                    | 0.43 lb(US) (0.195 kg) |
| Operating position            | Any position           |
| Shape of signaling unit head  | Round                  |
| Head material                 | Plastic                |
| Operator position information | 3 positions            |
| Contacts type and composition | Without contact block  |
| Mechanical durability         | 5000000 cycles         |
| Device presentation           | Basic element          |

## Environment

|                                       |                                                                                                                |
|---------------------------------------|----------------------------------------------------------------------------------------------------------------|
| Protective treatment                  | TC                                                                                                             |
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C)                                                                                     |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C)                                                                                     |
| Overvoltage category                  | Class II IEC 61140                                                                                             |
| IP degree of protection               | IP66 IEC 60529                                                                                                 |
| NEMA degree of protection             | NEMA 1<br>NEMA 12<br>NEMA 13<br>NEMA 2<br>NEMA 3<br>NEMA 3R<br>NEMA 4<br>NEMA 6                                |
| Standards                             | EN/IEC 60947-5-1<br>EN/IEC 60947-1<br>EN/IEC 60947-5-4<br>JIS C 4520<br>JIS C 852<br>UL 508<br>CSA C22.2 No 14 |
| Product Certifications                | NEMA<br>UL 508                                                                                                 |
| Vibration resistance                  | 7 gn 2...500 Hz)IEC 60068-2-6                                                                                  |
| Shock resistance                      | 50 gn IEC 60068-2-27                                                                                           |

## Ordering and shipping details

|                       |                               |
|-----------------------|-------------------------------|
| Category              | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule     | CS1                           |
| Nbr. of units in pkg. | 1                             |
| Package weight(Lbs)   | 0.5 lb(US) (0.23 kg)          |
| Returnability         | No                            |
| Country of origin     | MX                            |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                             |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                       |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                           |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                              |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                         |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                         |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                      |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                               |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                                                                |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001KR8W](#)