



Main

Range of Product	Harmony XAC
Product or Component Type	Contact block
Component name	ZB2
Electrical circuit type	Control circuit
Contact block application	Up / down operator
Contact block type	Single
Type of operator	Spring return
Product Compatibility	XACA
Contacts type and composition	1 NO
Mounting of block	Front mounting
Contact operation	Staggered Slow-break

Complementary

Connections - terminals	Screw clamps terminals, 1 x 2.5 mm ² with or without cable end Screw clamps terminals, 2 x 1.5 mm ² with or without cable end
Mechanical durability	1000000 cycles
Contact code designation	A600 AC-15, U _e = 240 V, I _e = 3 A IEC 947-5-1 appendix A A600 AC-15, U _e = 600 V, I _e = 1.2 A IEC 947-5-1 appendix A Q600 DC-13, U _e = 250 V, I _e = 0.27 A IEC 947-5-1 appendix A Q600 DC-13, U _e = 600 V, I _e = 0.1 A IEC 947-5-1 appendix A
[I _{th}] conventional enclosed thermal current	10 A
[U _i] rated insulation voltage	600 V 3) IEC 60947-1
[U _{imp}] rated impulse withstand voltage	6 kV IEC 60947-1
Maximum resistance across terminals	25 MOhm
Operating force	13...15 N
Short-circuit protection	10 A fuse protection cartridge gG (gl)
Rated operational power in W	40 W DC-13 1000000 cycles 3600 cyc/h 120 V 0.5 IEC 60947-5-1 48 W DC-13 1000000 cycles 3600 cyc/h 48 V 0.5 IEC 60947-5-1 65 W DC-13 1000000 cycles 3600 cyc/h 24 V 0.5 IEC 60947-5-1
Terminals description ISO n°1	(13-14)NO_CL
Net Weight	0.03 lb(US) (0.015 kg)

Environment

Standards	EN/IEC 60204-32 UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Vibration resistance	15 gn 10...500 Hz) IEC 60068-2-6
Shock resistance	100 gn IEC 60068-2-27
Electrical shock protection class	Class II IEC 61140

Ordering and shipping details

Category	22466-PUSHBUTTON, ACCESSORIES
Discount Schedule	CS2
GTIN	3389110612547
Nbr. of units in pkg.	1
Package weight(Lbs)	0.53 oz (15 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.59 in (1.5 cm)
Package 1 width	1.57 in (4 cm)
Package 1 Length	1.57 in (4 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	5.40 oz (153 g)
Package 2 Height	1.97 in (5 cm)
Package 2 width	7.87 in (20 cm)
Package 2 Length	7.87 in (20 cm)
Unit Type of Package 3	S02
Number of Units in Package 3	120
Package 3 Weight	4.78 lb(US) (2.168 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZB2BE201](#)