

Product data sheet

Characteristics

XAPG29502

die-cast empty control station - XAP-G -Ø 22 mm-80x130mm front plate-undrilled

Product availability: Stock - Normally stocked in distribution facility



Main

Range of product	Harmony XAP
Product or component type	Die-cast empty control station
Device short name	XAPG
Product destination	For Ø 22 mm control and signalling units
Product front plate size	80 x 130 mm
Usable depth	2.93 in (74.5 mm)
Number of cut-out	Undrilled
Colour of base of enclosure	Grey RAL 7032
Colour of cover	Grey RAL 7032
Material	Zinc alloy
Cable entry	1 hole with blanking plug for cable gland with <= 0.55 in (14 mm) 1 hole without blanking plug for cable gland with <= 0.55 in (14 mm)
Product mounting	Flush mounting
IP degree of protection	IP65 conforming to IEC 60529 IP657 conforming to NF C 20-010

Complementary

Product weight	0.959 kg
----------------	----------

Environment

Protective treatment	TC
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Electrical shock protection class	Class I conforming to IEC 60536 Class I conforming to NF C 20-030

Ordering and shipping details

Category	22475 - WALL STATIONS
Discount Schedule	CS2
GTIN	00785901186762
Nbr. of units in pkg.	1
Package weight(Lbs)	2.1000000000000001
Returnability	Y
Country of origin	MA

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XAPG29502](#)