

Product availability: Non-Stock - Not normally stocked in distribution facility



## Main

Range of product	Harmony XB5 Harmony XB4
Product or component type	Block for test light
Product compatibility	BA 9s Integral LED
Light block type	Single block for test light function
[Us] rated supply voltage	12 V AC/DC 24 V AC/DC 24...120 V AC/DC
Electrical connection	1 wire

## Complementary

Electrical shock protection class	Class I Harmony XB4 conforming to IEC 60536 Class II Harmony XB5 conforming to IEC 60536
Product weight	0.02 lb(US) (0.01 kg)

## Environment

Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Standards	IEC 60947-1 IEC 60947-5-5 EN 60947-5-5 EN 60947-5-4 CSA C22.2 No 14 JIS C 4520 IEC 60947-5-1 IEC 60947-5-4 EN 60947-5-1 EN 60947-1 UL 508
Product certifications	GL BV DNV UL listed LROS (Lloyds register of shipping) RINA CSA
Vibration resistance	5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn 18 ms conforming to IEC 60068-2-27 50 gn 11 ms conforming to IEC 60068-2-27

## Ordering and shipping details

Category	22469 - PUSHBUTTON,22MM ACCESSORIES-NEW
Discount Schedule	CS2
GTIN	003389118030107
Nbr. of units in pkg.	1
Package weight(Lbs)	4.0000000000000001E-2
Returnability	N
Country of origin	FR


Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

Contractual warranty

Warranty period	18 months
-----------------	-----------

## Wiring Diagram



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZBZG156](#)