

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Harmony XVC1
Product or component type	Complete pre-wired monolithic tower light
Beacon or indicator bank unit type	1 illuminated unit
Sound signalling	Without
Mounting diameter	3.94 in (100 mm)
Component name	XVC
Light source	Red LED steady or flashing signalling
[Us] rated supply voltage	24 V
Supply circuit type	DC

Complementary

Material	Illuminated unit: polycarbonate Base unit: ABS (acrylonitrile butadiene-styrene) Top cover: PBT + ABS (UL94-V0)
Product mounting	On base
Cable cross section	0 in ² (0.83 mm ²) 0 in ² (0.33 mm ²)
AWG gauge	AWG 18 AWG 22
Cable length	19.69 in (500 mm)
Marking	CE
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	100 mA
Flashing frequency	0.7...3 Hz
Product weight	1.54 lb(US) (0.7 kg)
Height	8.5 in (216 mm)


Environment

Standards	EN/IEC 61000-6-3 EN/IEC 61000-6-2 EN/IEC 61000-6-4
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-31...158 °F (-35...70 °C)
Ambient air temperature for operation	-22...122 °F (-30...50 °C)
Electrical shock protection class	Class II conforming to EN/IEC 61140
IP degree of protection	IP54 conforming to EN/IEC 60529

Ordering and shipping details

Category	22617 - XVC TOWER LIGHTS
Discount Schedule	XV
GTIN	00785901707639
Nbr. of units in pkg.	1
Package weight(Lbs)	3.0300000000000002
Returnability	N
Country of origin	JP

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0808 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------


Dimensions

No. of illuminated units	b in mm	b in in.
1	216	8.50
2	294	11.57
3	372	14.65
4	450	17.72
5	528	20.79

Pre-assembled and Pre-wired Tower Light

Mounting on Horizontal Support (Direct or with Fixing Plate)

Panel cut-out

$$\frac{mm}{in.}$$


Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XVC1B1K](#)