

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Harmony
Product or component type	Digital display head
Mounting diameter	0.87 in (22 mm)
Cap/operator or lens colour	Red
[Us] rated supply voltage	24 V DC

Complementary

Display type	7 segments LED + decimal point
Supply voltage limits	13...30 V
Product weight	0.04 lb(US) (0.02 kg)

Environment

Product certifications	CSA UL
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Vibration resistance	10 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	180 gn conforming to IEC 60068-2-27
Electrical shock protection class	Class II conforming to NF C 20-030
IP degree of protection	IP65 conforming to IEC 60529 IP65 conforming to NF C 20-010

Ordering and shipping details

Category	22460 - PUSHBUTTONS 22MM (PLASTIC)
Discount Schedule	CS2
GTIN	00785901248743
Nbr. of units in pkg.	1
Package weight(Lbs)	4.0000000000000001E-2
Returnability	N
Country of origin	FR

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZA2VA04](#)