

Product data sheet

Characteristics

SM952A400076

Hyde Park, superprox ultrasonic dual level sensor

Main

| | |
|---------------------------|-----------------------------|
| Range of Product | Hyde Park |
| Sensor Type | Ultrasonic sensor |
| Series name | Standard format |
| Device short name | SM952 |
| Sensor design | Ø 30 mm |
| Material | Stainless steel |
| [Us] rated supply voltage | 12...24 V DC |
| Electrical connection | 1 connector micro |
| [Sd] sensing range | 0.39...6.56 ft (0.12...2 m) |
| IP degree of protection | IP66 |

Complementary

| | |
|------------------------|---------|
| Type of sensing window | Fixed |
| Enclosure Material | Plastic |
| Transmission frequency | 75 kHz |
| Maximum delay response | 35 ms |

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 22490 - SENSORS-ULTRASONIC (XX5,6) |
| Discount Schedule | DS2 |
| GTIN | 03389119119764 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.08 lb(US) (0.04 kg) |
| Returnability | No |
| Country of origin | US |

Offer Sustainability

| | |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SM952A400076](#)