



Main

Product or Component Type	Industrial Control Transformer
Range of Product	Instakits

Complementary

Phase	3 phase 1 phase
Rated power in VA	50 VA
Primary voltage	600 V
Secondary Voltage	24 V
Electrical Connection	Connector

Environment

Product Certifications	CSA UL
------------------------	-----------

Ordering and shipping details

Category	18074 - SPARE PARTS DISCOUNT I11
Discount Schedule	I11
GTIN	00785901690221
Nbr. of units in pkg.	1
Package weight(Lbs)	3.07 lb(US) (1.39 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	5.70 in (14.478 cm)
Package 1 width	4.20 in (10.668 cm)
Package 1 Length	5.90 in (14.986 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Contractual warranty	
Warranty	18 months

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LA9TFD32A](#)