



Main

Product or Component Type	Full voltage starter
Range of Product	Instakits
Motor starter type	Non reversing
Disconnecter device type	Powerpact motor circuit protector

Complementary

[Ue] rated operational voltage	120 V AC 50/60 Hz
[Ie] rated operational current AC	9 A
Maximum Horse Power Rating	0.3 Hp 120 V AC, 1 phase 1 Hp 240 V AC, 1 phase 2 Hp 208 V AC, 3 phase 2 Hp 230 V AC, 3 phase 5 Hp 460 V AC, 3 phase 7.5 hp 575 V AC, 3 phase
[Uc] control circuit voltage	600 V AC
Auxiliary contact composition	1 NO + 1 NC
Protection Type	Motor circuit protector 30 A
Location of connection	Line

Environment

Product Certifications	UL CSA IEC
NEMA degree of protection	NEMA 12 steel

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LE1D099E72OG70](#)