



Main

Product or Component Type	Full voltage starter
Range of Product	Instakits
Motor starter type	Non reversing






Complementary

[Ue] rated operational voltage	24 V AC 50/60 Hz
[Ie] rated operational current AC	18 A
Maximum Horse Power Rating	25 Hp 575 V AC, 3 phase 5 Hp 208 V AC, 3 phase 5 Hp 230 V AC, 3 phase 10 hp 460 V AC, 3 phase
[Uc] control circuit voltage	600 V AC
Auxiliary contact composition	1 NO + 1 NC
Location of connection	Line

Environment

Product Certifications	UL CSA IEC
NEMA degree of protection	NEMA 1 steel

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
PVC free	Yes

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LE1D183A62OB70](#)