



Main

| | |
|---------------------------|-----------------------------------|
| Product or Component Type | Full voltage starter |
| Range of Product | Instakits |
| Motor starter type | Non reversing |
| Disconnecter device type | Powerpact motor circuit protector |

Complementary

| | |
|-----------------------------------|--|
| [Ue] rated operational voltage | 120 V AC 50/60 Hz |
| [Ie] rated operational current AC | 18 A |
| Maximum Horse Power Rating | 25 Hp 575 V AC, 3 phase 5 Hp 208 V AC, 3 phase 5 Hp 230 V AC, 3 phase 10 hp 460 V AC, 3 phase |
| [Uc] control circuit voltage | 600 V AC |
| Auxiliary contact composition | 1 NO + 1 NC |
| Protection Type | Motor circuit protector 30 A |
| Location of connection | Line |

Environment

| | |
|---------------------------|------------------|
| Product Certifications | IEC CSA UL |
| NEMA degree of protection | NEMA 12 steel |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| PVC free | Yes |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LE1D189E72OG70](#)