

J15BLK

APC AV Black J Type 1.5kVA Power Conditioner with Battery Backup 120V Retail



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Battery modules ship installed Cat 6 Ethernet cable CD with software Removable heavy duty 12 gauge input power cord Removable support feet User Manual USB cable
--------------------	--

Physical

Cable length	10 ft (3.05 m)
Color	Black
Depth	17.99 in (45.7 cm)
Height	5.24 in (13.3 cm)
Net Weight	47.09 lb(US) (21.36 kg)
Width	17.01 in (43.2 cm)

Input

Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	NEMA 5-15P
Efficiency at full load	90...140 V
Maximum Input Current per Phase	12 A
Switching current capacity	15 A
Nominal Input Voltage	120 V

Output

Kw Rating	865 W
Max Configurable Power (Watts)	865 W
Output Frequency (sync to mains)	47...63 Hz sync to mains
Topology	Line Interactive
Waveform Type	Stepped approximation to a sinewave
Nb of power socket outlets	12 NEMA 5-15R
Output voltage	120 V

Conformance

Product Certifications	CSA
Standards	FCC Part 15 class B FCC part 68 UL 1778 UL 498
Equipment protection policy	Lifetime : \$750000

Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Batteries & Runtime

Battery Type	Lead-Acid battery
Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	16 h
Liquid Electrolyte Value	0

Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rating	4500 J
Filtering	Full time multi-pole noise filtering : 0.7% IEEE surge let-through : zero clamping response time : m
Data line protection	RJ11 Modem/Fax protection (four wire dual line) RJ45 10/100 Base-T Ethernet protection Cable modem/video protection Co-axial Video / Cable protection Coaxial 2-Way splitter with protection



Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	PH

Packing Units

Package 1 Height	12.99 in (33 cm)
Package 1 width	21.50 in (54.6 cm)
Package 1 Length	24.02 in (61 cm)
SCC14	107313040
Number of Units in Package 2	1
Number of Units in Package 3	6

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Optimized Energy Efficiency	Energy efficient product

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[J15BLK](#)