



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Device short name	KY
Enclosure type	Weatherproof enclosure dust and oil resistant in-door/outdoor
Mounting diameter	1.18 in (30 mm)
Provided equipment	Contact block 2 KA1 Legend plate 1 KN203 Legend plate 1 KN204

Complementary

Line Rated Current	10 A
Contacts type and composition	2 NO + 2 NC
Control type	Push-button 1 9001KR1B Push-button 1 9001KR3R
Device mounting	Surface
Electrical connection	Screw clamp terminal
Enclosure material	Die cast zinc alloy grey
Marking	ON-OFF
Operator profile	2 projecting push-buttons
Permissible voltage	<= 300 V

Environment

NEMA degree of protection	NEMA 3/4/13
Product certifications	CE CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR

Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901039891
Nbr. of units in pkg.	1
Package weight(Lbs)	3.73
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1002 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:

----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001KYK218](#)