

## Product data sheet

### Characteristics

## VA1

L100/300 limit switch lever - aluminum - adj.  
75°-180° fork - outside rollers

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

Range of product	L100/300
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	L100/300
Associated complete product	HL100 HL300 HML100 HML300 L100 L300 ML100 ML300
Movement of operating head	Rotary
Type of operator	Aluminium stay put forked arm with rollers length: 2.5 in - offset: - adjustable angle 75° to 180° forked arm with rollers
Type of roller	2 steel outside roller diameter: 1 in - width: 0.25 in
Type of approach	Lateral approach
Positive opening	Without

### Complementary

Switch actuation	By specific cam
Product weight	0.1 lb(US)

### Environment

Ambient air temperature for operation	-10...185 °F
Ambient air temperature for storage	-10...185 °F
Environmental characteristic	Standard environment

### Ordering and shipping details

Category	21519 - 9007 MISCELLANEOUS
Discount Schedule	DS1
GTIN	00785901122531
Nbr. of units in pkg.	1
Package weight(Lbs)	0.10000000000000001
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and

----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[VA1](#)