

Product availability: Stock - Normally stocked in distribution facility



### Main

Range	TeSys
Device short name	LUA8
Product or component type	Auxiliary contact


### Complementary

Auxiliary contact composition	2 NO
Signalling function	Start-stop
System Voltage	24...250 V AC 24...250 V DC
[I <sub>th</sub> ] conventional free air thermal current	5 A
Minimum switching voltage	17 V
Minimum switching current	5 mA
Product weight	0.11 lb(US) (0.048 kg)
Connections - terminals	Screw clamp terminals

### Ordering and shipping details

Category	22399 - TESYS U, ACCESSORIES
Discount Schedule	I11
GTIN	00785901291954
Nbr. of units in pkg.	1
Package weight(Lbs)	0.13
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1301 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LUA8E20](#)