

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Magelis iPC
Product or component type	Serial line interface
Accessory / separate part category	Connection accessory

Complementary

Accessory / separate part destination	Magelis iPC with Mini PCIe slot
Integrated connection type	Mini PCIe full-size with 1 SUB-D 32 RS232, transmission rate: 50 bit/s...230.4 kbit/s 2 m cable
Input current	500 mA at 3.3 V DC
Range compatibility	Magelis iPC
Width	2.99 in (76 mm)
Height	3.19 in (81 mm)
Depth	1.5 in (38.2 mm)

Environment

Ambient air temperature for operation	-4...140 °F (-20...60 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Relative humidity	5...95 % non-condensing

Ordering and shipping details

Category	22574 - MAGELIS BOX PC AND PANEL PC
Discount Schedule	MC2
GTIN	00785901672289
Nbr. of units in pkg.	1
Package weight(Lbs)	0.2999999999999999
Returnability	N
Country of origin	TW

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[HMIYMINSL42321](#)