

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Magelis iPC
Product or component type	Power supply module
Accessory / separate part category	Electrical accessory

Complementary

Product weight	1.76 lb(US) (0.8 kg)
Accessory / separate part destination	Magelis HMIBM Magelis HMIDAD
Input voltage	100...240 V AC at 47...63 Hz
Output voltage	24 V DC
Line Rated Current	4.6 A
Associated fuse rating	3.15 A

Environment

Ambient air temperature for operation	32...122 °F (0...50 °C)
Product certifications	ATEX CE CULus CULus HazLoc Class I Division 2 ANSI/ISA 12-12-01 CULus HazLoc Class I Division 2 CSA 22-2 No 213 IEC Ex hazardous locations 3GD zone 2/22 UL 60950 CSA 60950

Ordering and shipping details

Category	22575 - MAGELIS MC3
Discount Schedule	MC3
GTIN	00785901719366
Nbr. of units in pkg.	1
Package weight(Lbs)	2.6000000000000001
Returnability	N
Country of origin	TW

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1604 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[HMIYMMAC1](#)