



Main

Body type	Compact
Device short name	XCKD
Range of Product	OsiSense
Series name	General duty

Complementary

Line Rated Current	10 A
Associated body	ZCD21
Associated head	ZCE01
Body material	Metal
Contact operation	Snap action
Height	2.17...3.96 in (55...100.5 mm)
Positive opening	With
Net Weight	0.54 lb(US) (0.24 kg)
Size	Roller 50 x 10 mm
Switch actuation	CW and CCW
Torque value	14.16 ozf.in

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
IP Degree of Protection	IP66 IP67
NEMA Degree of Protection	NEMA 1/2/4/6/12/13
Product certifications	CSA CE UL Listed
Shock resistance	50 gn
Standards	CENELEC EN 50047
Vibration resistance	25 gn

Ordering and shipping details

Category	22418-LIMIT SWITCH,IEC,XCKP&XCKT
Discount Schedule	T
GTIN	785901703327
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XCKD2149N12](#)