

## ZCKD05

limit switch head ZCKD - without lever spring  
return left and or right actuation





Main

|                           |                                                                                                                      |
|---------------------------|----------------------------------------------------------------------------------------------------------------------|
| Range of product          | OsiSense XC                                                                                                          |
| Series name               | Standard format                                                                                                      |
| Product or component type | Limit switch head                                                                                                    |
| Device short name         | ZCKD                                                                                                                 |
| Head type                 | Rotary head                                                                                                          |
| Product compatibility     | XCKL<br>XCKM<br>XCKS                                                                                                 |
| Associated lever          | ZCKY31<br>ZCKY33<br>ZCKY34<br>ZCKY39<br>ZCKY41<br>ZCKY43<br>ZCKY49<br>ZCKY54<br>ZCKY55<br>ZCKY59<br>ZCKY81<br>ZCKY91 |

|                            |                                                |
|----------------------------|------------------------------------------------|
| Associated body            | ZCKL1                                          |
|                            | ZCKL1H7                                        |
|                            | ZCKL5                                          |
|                            | ZCKL5H7                                        |
|                            | ZCKL6                                          |
|                            | ZCKL6H7                                        |
|                            | ZCKL7                                          |
|                            | ZCKL7H7                                        |
|                            | ZCKL8                                          |
|                            | ZCKL8H7                                        |
|                            | ZCKLD31                                        |
|                            | ZCKLD31H7                                      |
|                            | ZCKLD35                                        |
|                            | ZCKLD35H7                                      |
|                            | ZCKLD37                                        |
|                            | ZCKLD37H7                                      |
|                            | ZCKLD39                                        |
|                            | ZCKLD39H7                                      |
|                            | ZCKM1                                          |
|                            | ZCKM1H29                                       |
|                            | ZCKM1H7                                        |
|                            | ZCKM5                                          |
|                            | ZCKM5H29                                       |
|                            | ZCKM5H7                                        |
|                            | ZCKM6                                          |
|                            | ZCKM6H29                                       |
|                            | ZCKM6H7                                        |
|                            | ZCKM7                                          |
|                            | ZCKM7H29                                       |
|                            | ZCKM7H7                                        |
|                            | ZCKM8                                          |
|                            | ZCKM8H29                                       |
|                            | ZCKM8H7                                        |
|                            | ZCKM9                                          |
|                            | ZCKM9H29                                       |
|                            | ZCKMD31                                        |
|                            | ZCKMD31H29                                     |
|                            | ZCKMD31H7                                      |
|                            | ZCKMD35                                        |
|                            | ZCKMD35H29                                     |
|                            | ZCKMD35H7                                      |
|                            | ZCKMD37                                        |
|                            | ZCKMD37H29                                     |
|                            | ZCKMD37H7                                      |
|                            | ZCKMD39                                        |
|                            | ZCKMD39H29                                     |
|                            | ZCKMD39H7                                      |
|                            | ZCKS1                                          |
|                            | ZCKS1H29                                       |
|                            | ZCKS2                                          |
|                            | ZCKS2H29                                       |
|                            | ZCKS404H29                                     |
|                            | ZCKS5                                          |
|                            | ZCKS5H29                                       |
|                            | ZCKS6                                          |
|                            | ZCKS6H29                                       |
|                            | ZCKS7                                          |
|                            | ZCKS7H29                                       |
|                            | ZCKS8                                          |
|                            | ZCKS8H29                                       |
|                            | ZCKS9                                          |
|                            | ZCKS9H29                                       |
|                            | ZCKSD31                                        |
|                            | ZCKSD31H29                                     |
|                            | ZCKSD35                                        |
|                            | ZCKSD35H29                                     |
|                            | ZCKSD37                                        |
|                            | ZCKSD37H29                                     |
|                            | ZCKSD39                                        |
|                            | ZCKSD39H29                                     |
| Movement of operating head | Rotary                                         |
| Type of operator           | Without operating lever spring return          |
| Type of approach           | Lateral approach 1 or 2 programmable direction |

## Complementary

|                  |                                         |
|------------------|-----------------------------------------|
| Switch actuation | From left and/or right<br>CW and/or CCW |
| Positive opening | With<br>Without                         |
| Head material    | Plastic                                 |

## Environment

|                                       |                            |
|---------------------------------------|----------------------------|
| Ambient air temperature for operation | -13...158 °F (-25...70 °C) |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C) |
| Environmental characteristic          | Standard environment       |

## Ordering and shipping details

|                       |                                 |
|-----------------------|---------------------------------|
| Category              | 22416 - LIMIT SWITCHES,IEC,XCKL |
| Discount Schedule     | T                               |
| GTIN                  | 00785901647034                  |
| Nbr. of units in pkg. | 1                               |
| Package weight(Lbs)   | 0.16                            |
| Returnability         | Y                               |
| Country of origin     | ID                              |

## Offer Sustainability

|                                  |                                                                                                                                    |
|----------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status         | Green Premium product                                                                                                              |
| RoHS (date code: YYWW)           | Compliant - since 1012 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold                                                                                  |
| Product end of life instructions | Need no specific recycling operations                                                                                              |
| California proposition 65        | WARNING: This product can expose you to chemicals including:                                                                       |
| ----- Substance 1                | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and                                        |
| ----- Substance 2                | Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.          |
| ----- More information           | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                      |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZCKD05](#)